

# MW 3000

Ergonomic right-hand mouse with additional buttons



Models may vary from the image shown

The CHERRY MW 3000 is an advanced 6-button wireless mouse with 2.4 GHz technology and an ergonomic design specially for right-handers. Its nano USB receiver is so small that it can safely stay inside the notebook even when you're on the move – the mouse is always ready for use. The CHERRY MW 3000 has a precise optical sensor and offers maximum energy efficiency thanks to its technical design. Used along with the on/off switch, this ensures a long battery lifespan. High-quality materials, non-slip surfaces and sophisticated ergonomics make the CHERRY MW 3000 wireless mouse what it is – a faithful companion in the office and the home.

## FUNCTION AND PERFORMANCE

- Rubber grips on sides
- Nano USB receiver: able to stay in the notebook permanently
- 6-button mouse with an optical sensor and adjustable resolution (1000/1750 dpi)
- Optimised for use with the right hand
- Interference-free wireless 2.4 GHz technology (range of up to 10 meters)

## TECHNICAL DATA

Weight main product:	4 oz
Dimensions product without packaging:	4,17 in x 2,68 in x 1,54 in
Weight of product incl. packaging (g):	7.34 oz
Dimensions product incl. packaging:	4,8 in x 3,27 in x 2,05 in
Content of master carton (pieces):	10
Weight of master carton incl. content (g):	67.02 oz
Dimensions master carton:	5.71 in x 10.83 in x 6.89 in
Storage temperature:	5 °F - 140 °F
Working temperature:	32 °F - 104 °F
Max. Current consumption (mA)	2,5 mA
Mouse:	
Product approvals:	<ul style="list-style-type: none"><li>• CE</li><li>• cTÜVus</li><li>• FCC</li><li>• China RoHS</li><li>• UKCA</li></ul>
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"><li>• Windows 7</li><li>• Windows 8</li><li>• Windows 10</li><li>• Windows 11</li></ul>
Scope of delivery:	<ul style="list-style-type: none"><li>• 2 x AAA battery</li><li>• Manual</li><li>• Mouse</li><li>• Nano-USB-Receiver</li></ul>
Reliability:	MTBF > 80.000 Stunden
Switch type:	clicky
Number of keys:	6
Thumb buttons:	yes
Max. resolution (dpi):	1.750 dpi
dpi switch:	yes
dpi levels:	2
Illumination:	no
Software support:	CHERRY KEYS

USB dongle:	yes
2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	no
Wireless range (m):	33 ft
Connection via Bluetooth:	no
Number of batteries:	2
Battery type:	Alkaline
Battery design:	AAA
Battery rechargeable:	no

Battery replaceable:	yes
Battery charging socket:	no
Model number:	JF-T01REV
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.

EAN & Part number	Color	Illumination	Country version
4025112076657 JW-T0100	black	no	Europe / USA
4025112098789 JW-T0102	black	no	Asia

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.