



NOTE:


- 1 .ELECTRICAL CHARACTERISTICS
  - 1-1 RATING CURRENT: 2A AC/DC
  - 1-2 RATING VOLTAGE: 250V AC/DC
  - 1-3 INSULATION RESISTANCE: 1000M OHMS MIN
  - 1-4 WITHSTANDING VOLTAGE: 800V AC/1MINUTE
  - 1-5 OPERATING TEMPERATURE: -40°C~+105°C
2. MATERIAL:
 

PA66, UL 94V-0, NATURAL COLOR
3. USED WITH AFCI 10156615
4. PRODUCT SPEC: GS-12-1594
5. ORDERING CODE: 10156614-XX 0 X LF

NUMBER OF PINS ——— PACKAGE  
 02~16: 02~16PINS                      0: BAG



POS	DIMENSIONS(MM)		POS	DIMENSIONS(MM)	
	A	B		A	B
2	2.00	5.20	10	18.00	21.20
3	4.00	7.20	11	20.00	23.20
4	6.00	9.20	12	22.00	25.20
5	8.00	11.20	13	24.00	27.20
6	10.00	13.20	14	26.00	29.20
7	12.00	15.20	15	28.00	31.20
8	14.00	17.20	16	30.00	33.20
9	16.00	19.20			



mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 101	projection	product family
ltr		ecn no	dr	date	MINITEK
A		New release	Jason	2020-2-19	title
		angles	linear	.X±.3 .XX±.20 .XXX±.10	2.OPITCH BOARD-IN, Vertical , HOUSING
		0°±x'		mm	dwg no
		dr	Jason Wang	2020-1-19	sheet 1 of 1
		enr	Jason Wang	2020-2-19	size
		chr	-	-	10156614
		app	Tim Yao	2020-2-19	type
sheet index		revision sheet	A	1	Product Customer Drawing

Amphenol FCI

© 2016 AFCI