






D

A

B

C

LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW



GENERAL CHARACTERISTICS : SEE DRAWING C01-8639-0001

DAV3V3P300G30	UNC 4.40
DAV3V3P300G40	UNC 4.40
DAV3V3P300H30	UNC 4.40
DAV3V3P300H40	UNC 4.40
DAI3V3P300G30	M3
DAI3V3P300G40	M3
DAI3V3P300H30	M3
DAI3V3P300H40	M3
PART NUMBER	Threaded A

European Views

www.fciconnect.com		surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED							
ANGULAR		LINEAR		0.X ±0.1		size A3	
0.XX ±2°				0.XX ±0.1		Scale 2	
0.XXX ±0.1				ECN LS07-0094		Spec ref -	
Product family		SUB		ECN		LS07-0094	
Product family		SUB		Spec ref -			
FCi		PIN CONNECTOR SUB D WITH POWERS CONTACTS				Rev. E	
catalog no		-				C01-8639-1517	
CUSTOMER		-				sheet 1 of 1	

rev	ecn no	dr	date
D	-	MPE	2003/11/07
E	LS07-0094	MPE	2007/04/05
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-