



4203

HPDB50F	ID50M	HPDB50F	ID50M
1	1	26	2
2	3	27	4
3	5	28	6
4	7	29	8
5	9	30	10
6	11	31	12
7	13	32	14
8	15	33	16
9	17	34	18
10	19	35	20
11	21	36	22
12	23	37	24
13	25	38	26
14	27	39	28
15	29	40	30
16	31	41	32
17	33	42	34
18	35	43	36
19	37	44	38
20	39	45	40
21	41	46	42
22	43	47	44
23	45	48	46
24	47	49	48
25	49	50	50

*NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION	Q'TY	Supplier
4	SCREW 3.8*6.35 2-56# F38X635-2560-0YN	2	M095
3	BRACKET HPDB50 FEMALE, NICKEL PLATED	1	M901
2	ID50 MALE PCB TYPE	1	M922
1	PCB SCSI-2	1	M730
	HPDB50 FEMALE PCB TYPE	1	M083

APPROVED			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED	HU		
DRAWING	XIAO		
DATE	30/MAR/17		
ITEM NO.	IDC-50FM-AD	UNIT:mm	