

# Datasheet for 76650-0061

General Information				
Part Number:	76650-0061			
Manufacturer:	Molex / Waldom			
Title:	.093" Power Connector Kit			
Description:	Free Hanging Plug and Receptacle, 1 Circuit			
Product Family:	Standard .093"			
Certificates:	(Molex parts within this kit) - EU and China RoHS, UL, CSA and TUV			
Country of Origin:	Kit assembled in U.S.A.			
Specifications				

Design Configuration:	Wire to Wire
Pitch:	5.03mm (.198 ")
Connector Type:	Plug and Receptacle
Mounting Orientation:	Free-hanging
Circuit Sizes:	1
Current Rating:	5 Amps
Voltage:	600 Volts
Wire size:	22-18 AWG

## **Product Highlights**

The Standard .093" is a durable and economical power or signal connector, capable of carrying up to 12 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .093" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications.

Features and Benefits	Applications
<ul> <li>Male and female terminals may be used in either plug or receptacle housings</li> <li>Free hanging or panel mount housing version available</li> <li>Round terminals may be oriented in any direction for fast assembly</li> </ul>	<ul> <li>Power Supplies</li> <li>Appliances</li> <li>Gaming Machines</li> <li>Vending Machines</li> <li>Refrigerators</li> <li>Washing Machines</li> <li>Copy Machines</li> </ul>



## Datasheet for 76650-0061

## Bill of Materials for Part No. 76650-0061

Molex Part No.	Country of Origin	Description	Quantity in Kit
02-09-1119	USA	.093" Dia. Crimp Female Socket Terminals, 22-18 AWG	7
02-09-2118	USA	.093" Dia. Crimp Male Pin Terminals, 22-18 AWG	7
03-09-1011	USA	1-Circuit Panel Mount Nylon Connector Receptacle	5
03-09-2011	USA	1-Circuit Panel Mount Nylon Connector Plug	5

## Recommended Molex Tool(s) for Part No. 76650-0061\*

Molex Part No.	Country of Origin	Description
63819-1200 *	Sweden	Hand Crimp Tool
11-03-0006 *	Sweden	Extraction Tool
11-02-0003 *	Sweden	Insertion Tool

\*Tools not included in kit. Tools ordered separately.