1801 Morgan Street Rockford, Illinois 61102 800-435-2931 www.molexkits.com



Datasheet for 76650-0079

General Information

Part Number: 76650-0079

Manufacturer: Molex / Waldom

Title: Mini-Fit Jr. Connector Kit

Description: Plug and Receptacle, 12 Circuit

Product Family: Mini-Fit Jr.™

Certificates: (Molex parts within this kit) - EU RoHS, China RoHS, UL, CSA and TUV

Country of Origin: Kit assembled in U.S.A.

Specifications

Design

Configuration: Wire-to-Wire

Pitch: 4.2mm (.165")

Connector Type: Plug and Receptacle

Mounting

Orientation: Panel Mount

Circuit Sizes: 12

Current Rating: 6 Amps
Voltage: 600 Volts
Wire size: 24-18 AWG

Product Highlights

The Mini-Fit Jr. Series is designed for high current/high density applications. The Mini-Fit Jr. is appropriate for both power and signal applications. The Mini-Fit product family accepts the same terminals and application tooling, further reducing your design and qualification effort.

Features and Benefits

- Fully isolated terminals
- Positive housing locks
- Four point of contact for reliability
- Low engagement force terminals

Applications

- Security and Alarms
- Vending and Gaming Machines
- White Goods
- Production Equipment
- Broadcast Equipment
- Telecom Infrastructure



Datasheet for 76650-0079

Bill of Materials for Part No. 76650-0079				
Molex Part No.	Country of Origin	Description	Quantity in Kit	
39-00-0039	USA	Crimp Type Female Socket Terminals, 24-18 AWG	12	
39-00-0041	USA	Crimp Type Male Pin Terminals, 24-18 AWG	12	
39-01-2120	USA	12 Circuit Free Hanging Receptacle, 4.20mm (.165") Pitch	1	
39-01-2121	USA	12 Circuit Panel Mount Plugs, 4.20mm (.165") Pitch	1	

Recommended Molex Tool(s) for Part No. 76650-0079* Country

Molex Part No.	of Origin	Description
63819-0900 *	Sweden	Hand Crimp Tool
11-03-0044 *	Sweden	Extraction Tool

^{*}Tools not included in kit. Tools ordered separately.