

Energizer® Vision Rechargeable Lantern - 1200L Upgrade

The *Energizer*® Rechargeable Lantern is a bright and powerful lighting option for various tasks. On top of being rechargeable, this light's high lumen output in combination with a long runtime and power bank capabilities provide a reliable 360 lighting for adventures, outdoor activities, emergency situations, and it can also be used to charge devices via a USB port out. The design provides a steady base for hands-free operation and the comfortable non-slip grip handle makes it easy to carry. With the *Energizer*® Rechargeable Lantern, you can customize the light output as needed by using its dimming feature, or for a low diffused light use the night light mode. Includes charging cable.

Design Benefits

- ✓ **Improved lumens to 1200L from 1000L**
- ✓ Durable construction
- ✓ Dimming Feature for customized light output and optimal runtime
- ✓ Powerful and bright 360° area lighting
- ✓ USB Port out – Charges Devices (Can operate in low mode **and** charge device. Must unplug USB cord to operate in high mode)

- ✓ Steady base for hands-free and comfortable non-slip grip handle makes it easy to carry
- ✓ Shatterproof lens

Performance Benefits

- ✓ Rechargeable – Fully Charge in 8 hours*
- ✓ Long runtime
- ✓ Up to 12x Brighter than standard LED technology
- ✓ High Mode for maximum brightness
- ✓ Night Light
- ✓ Powerful light even after a full smartphone charge




Light and Power Source

- ✓ Features LED technology
- ✓ Rechargeable Lithium-ion battery



ENALUH28



3 Operating Modes + Dimming		
Mode	Lumens	Runtime
High	1200	7hrs
Low	125	50hrs
Night Light	-	-

**Light must be turned off while charging.

**Based on an average smartphone battery of 1810 mAh capacity