




240 E. Rosecrans Avenue | Gardena, CA 90248 | (800) 234-5613 | www.ezlok.com

Ultrasonic/Heat Stake Insert for Plastic



SPECS:

Part No: TH-518-SV

Style: Tapered; Single Vane

Installation Method: Ultrasonic or Heat Staking

Material: Brass

For Use In: Thermoplastic

Internal Thread: 5/16-18

Overall Length/in (L): 0.335


Insert Diameter/in (W): 0.469

Pilot Diameter/in (N): 0.439

*Rec. Hole Size/in (D): 0.448

*Rec. Hole Size/in (S): 0.431

Hole depth should be a minimum of .030" greater than the insert length in blind holes.



* Hole size requirements may vary depending on a number of factors, including material and tools.
We recommend that you test your application prior to production.