



A		B	C	D	E
CAT. NO.	COLOR			REV	DESCRIPTION
109 - 160SD - 001	BLACK				
109 - 160SD - 002	WHITE/NATURAL				
					DATE



RoHS Compliant

NOTE:

1. FLAMMABILITY RATING : UL94V-2
2. MAX BUNDLE DIA. : 42 mm (1.65 inch)
3. MIN TENSILE STRENGTH : 50 lbs (22 kgs)
4. COLOR : SEE CHART

DRAWN: RYAN	Tolerance Unless Otherwise Specified
CHECKED: SCOTT	MATERIAL : PA66 UNIT: mm SCALE: 1/2
APPROVAL: JEFF	SHEET: 1-0 DATE: 2024/06/08

CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

CABLE TIES

PART NO:

109 - 160SD - X X X (SEE CHART)

1

2

3

4