




A		B	C	D		E
CAT. NO.	COLOR			REV	DESCRIPTION	DATE
109 - 2001 - 001	BLACK					
109 - 2001 - 002	WHITE/NATURAL					



RoHS Compliant

NOTE:

1. FLAMMBILITY RATING: UL94V-2
2. MAX BUNDLE DIA. : 52 mm (2.05 inch)
3. MIN TENSILE STRENGTH : 40 lbs ( 18 kgs)
4. COLOR: SEE CHART

DRAWN: RYAN	Tolerance Unless Otherwise Specified
CHECKED: SCOTT	MATERIAL: PA66
	UNIT: mm
	SCALE: 1/2
APPROVAL: JEFF	SHEET: 1-0
	DATE: 2024/06/08

**CnC Tech**

Industrial Cable and Connector Technology

DESCRIPTION:

CABLES TIES

PART NO:

109 - 2001 - X X X ( SEE CHART )

1

2

3

4