



A		B	C	D		E
CAT. NO.	COLOR			REV	DESCRIPTION	DATE
109 - 250S - 001	BLACK					
109 - 250S - 002	WHITE/NATURAL					



1

2

3

RoHS Compliant

- NOTE:
1. FLAMMBILITY RATING: UL94V-2
 2. MAX BUNDLE DIA. : 65 mm (2.56 inch)
 3. MIN TENSILE STRENGTH : 50 lbs (22 kgs)
 4. COLOR: SEE CHART

DRAWN: RYAN	Tolerance Unless Otherwise Specified
CHECKED: SCOTT	MATERIAL: PA66 UNIT: mm SCALE: 1/2
APPROVAL: JEFF	SHEET: 1-0 DATE: 2024/06/08

CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:	CABLES TIES
PART NO:	109 - 250S - X X X (SEE CHART)

4