



| A | | B | C | D | E |
|-------------------|---------------|---|---|-----|-------------|
| CAT. NO. | COLOR | | | REV | DESCRIPTION |
| 109 - 250SD - 001 | BLACK | | | | |
| 109 - 250SD - 002 | WHITE/NATURAL | | | | |
| | | | | | DATE |



RoHS Compliant

- NOTE:
1. FLAMMBILITY RATING : UL94V-2
 2. MAX BUNDLE DIA. : 74 mm (2.91 inch)
 3. MIN TENSILE STRENGTH : 50 lbs (22 kgs)
 4. COLOR : SEE CHART

| | |
|-------------------|-----------------------------------------|
| DRAWN: RYAN | Tolerance Unless Otherwise Specified |
| CHECKED: SCOTT | MATERIAL : PA66 |
| | UNIT: mm |
| | SCALE: 1/2 |
| APPROVAL: JEFF | SHEET: 1-0 |
| | DATE: 2024/06/08 |

CnC Tech
Industrial Cable and Connector Technology

DESCRIPTION: **CABLE TIES**

PART NO: **109 - 250SD - X X X (SEE CHART)**

1
2
3
4