

Product datasheet

Specifications

Fiber optic adaptor for Managed Switch - 10/100 BASE - LX



MCSEAAF1LFU00

Main

Range of product	Modicon
accessory / separate part category	Connection accessories
accessory / separate part type	Fiber optic adaptor
accessory / separate part designation	Fiber optic adaptor
accessory / separate part destination	LC connector port
Mode of transmission	Multi mode 50/125 µm Multi mode 62.5/125 µm

Complementary

Product compatibility	MCSESM switch TCSESM switch
Depth	50 mm
Port Ethernet	10/100BASE-LX
Width	20 mm
Height	18 mm
Net weight	0.04 kg

Environment

Ambient air temperature for operation	0...60 °C
---------------------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	12.500 cm
Package 1 Length	17.000 cm
Package 1 Weight	75.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm

Package 2 Weight 1.128 kg

Contractual warranty

Warranty 18 months

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins