



The DNA of tech.™



Additional In-House Backend Assembly Site for Industrial and Automotive Rectifiers in SMA, SMB and SMC Package

For further information, please contact your regional Vishay office.

CONTACT INFORMATION

Americas	Europe	Asia
Vishay Semiconductors One Greenwich Place - Shelton CT United States 06484 Phone: +1 402 563 6866 Fax: +1 402 563 6296 Diodes-Americas@vishay.com	Vishay Semiconductors Theresienstrasse 2 - Heilbronn Germany 74072 Phone: +49 7131 7498 656 (715) Fax: +49 7131 67 2938 Diodes-Europe@vishay.com	Vishay Semiconductors 37A Tampines Street 92 #07-01 - Singapore 528886 Phone: +65 6788 6668 Fax: +65 6788 988 Diodes-Asia@vishay.com

Description of Change: To support BCP (Business Continuity Program), Vishay Diodes Division is introducing an additional in-house back-end manufacturing site for products in SMA, SMB and SMC package.

This new assembly site is located in Kaohsiung, Taiwan. There is no change in form, fit and function on all involved part numbers.

Reason for Change: Capacity expansion and Risk management

Expected Influence on Quality/Reliability/Performance: No change in quality and reliability performance

Part Numbers/Series/Families Affected: Please see materials list on the succeeding page.

Vishay Brand(S): Vishay Semiconductors

Time Schedule:

Start Shipment Date: Thu Jan 16, 2025

Sample Availability: Available upon request

Product Identification: The new manufacturing code "K" will be marked next to the date code of device marking as the identification of additional manufacturing site, for example, "41K" (4 - 2024, 1 – January, K – Kaohsiung, Taiwan)

Qualification Data: Available upon request

This PCN is considered approved, without further notification, unless we receive specific customer concerns before Wed Jan 15, 2025 or as specified by contract.

Issued By: Fabio Modaro, fabio.modaro@vishay.com, Eddie Hwang, eddie.hwang@vishay.com



Product Change Notification



Product Group: DD/Fri Nov 15, 2024/PCN-DD-036-2024-REV-0

The DNA of tech.™

VS-1EMH01-M3/5AT	VS-1EMH02-M3/5AT	VS-2EMH01-M3/5AT	VS-2EMH02-M3/5AT	VS-2EGH01-M3/5BT
VS-2EGH02-M3/5BT	VS-3ECH01-M3/9AT	VS-3ECH02-M3/9AT	VS-10MQ040HM3/5AT	VS-10MQ040-M3/5AT
VS-10MQ040NTRPBF	VS-10MQ060HM3/5AT	VS-10MQ060-M3/5AT	VS-10MQ060NTRPBF	VS-10MQ100HM3/5AT
VS-10MQ100-M3/5AT	VS-10MQ100-M3Z/I	VS-10MQ100NTRPBF	VS-15MQ040HM3/5AT	VS-15MQ040-M3/5AT
VS-15MQ040-M3H/I	VS-15MQ040NTRPBF	VS-20MQ040HM3/5AT	VS-20MQ040-M3/5AT	VS-20MQ040NTRPBF
VS-20MQ060HM3/5AT	VS-20MQ060-M3/5AT	VS-20MQ060NTRPBF	VS-20MQ100HM3/5AT	VS-20MQ100-M3/5AT
VS-20MQ100NTRPBF	VS-30MQ040HM3/5AT	VS-30MQ040HM3H/I	VS-30MQ040-M3/5AT	VS-30MQ040-M3Z/I
VS-MBRA140-M3/5AT	VS-MBRA140TRPBF	VS-10BQ015HM3/5BT	VS-10BQ015-M3/5BT	VS-10BQ030HM3/5BT
VS-10BQ030-M3/5BT	VS-10BQ040HM3/5BT	VS-10BQ040-M3/5BT	VS-10BQ040-M3P/I	VS-10BQ060HM3/5BT
VS-10BQ060-M3/5BT	VS-10BQ100HM3/5BT	VS-10BQ100-M3/5BT	VS-20BQ030HM3/5BT	VS-20BQ030-M3/5BT
VS-MBRS1100-M3/5BT	VS-MBRS130L-M3/5BT	VS-MBRS130-M3/5BT	VS-MBRS140-M3/5BT	VS-MBRS190-M3/5BT
VS-30BQ015HM3/9AT	VS-30BQ015-M3/9AT	VS-30BQ040HM3/9AT	VS-30BQ040-M3/9AT	VS-30BQ060HM3/9AT
VS-30BQ060-M3/9AT	VS-30BQ100HM3/9AT	VS-30BQ100-M3/9AT	VS-MBRS340-M3/9AT	VS-MBRS360-M3/9AT