

Johanson Part Number Information

Johanson Part Number: SCDR302W222M4GV001E	Johanson Company: JDI	
Legacy P/N: 302S43W222MV3E-****-SC	Size for Capacitors (EIA): 1812	
Description: Capacitors Safety Caps, X2, 1812, X7R, 3000V, 2200pF±20%, Ni/Sn (RoHS), 7" Reel Embossed Tape	Specification	Number:
Life Cycle Stage:	UL60950,EN/UL/IEC60384-14	
AEC Q200 Qualified: 0	NCNR: 0	
Schedule B: 8532	Thickness (Max): 0.115	
ITAR: 0	Thickness (Min): None	
ECCN: EAR99	End Band(Min): 0.01	
RoHS Compliance: Yes, RoHS 10/10	End Band (max): 0.040	
	Standard Item: 1	
	Lead Time Typical (Weeks)*:*This can vary significantly so it is	
REACH: 1	important to obtain a quotation with lead time for production planning purposes.	
	13	
Country of Origin: None	Length (Min): 0.165	
Product Family: Capacitors	Length (Max): 0.185	
Product Subfamily: Capacitors Safety Caps	Width (Min):0.115	
Capacitance Value: 2200.000	Width (Max): 0.135	
Cap Unit of Meas: pF	Part Weight (mg): 150.00	
Tolerance: ±20%	Packaged Width (lb) Arm: None	
Voltage: 3000.0	Packaging: 7" Reel Embossed Tape	
Dielectric Temp Coefficient: X7R	Packaging Qty: None	
Termination: 68	Operating Temp Range: -55°C to +125°C	
Marking: Required Safety Mark	Storage Temp Range (Packaged): -65°C to +125°C	
	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%	
Product Release Date: Jan. 3, 2006, 8 a.m.		
Web	Page	Link:
https://www.johansondielectrics.com/ac-safety-capacitors		