

Johanson Part Number Information

Johanson Part Number: SCDP302G150J4GV001E	Johanson Company: JDI	
Legacy P/N: 302R29N150JV3E-****-SC	Size for Capacitors (EIA): 1808	
Description: Capacitors Safety Caps, X2, 1808, NP0/C0G, 3000V, 15pF±5%, Ni/Sn (RoHS), 7" Reel Embossed Tape	Specification	Number:
Life Cycle Stage:	UL60950,EN/UL/IEC60384-14	
AEC Q200 Qualified: 0	NCNR: 0	
Schedule B: 8532	Thickness (Max): 0.085	
ITAR: 0	Thickness (Min): None	
ECCN: EAR99	End Band(Min): 0.01	
RoHS Compliance: Yes, RoHS 10/10	End Band (max): 0.030	
	Standard Item: 1	
	Lead Time Typical (Weeks)*:*This can vary significantly so it is	
REACH: 1	important to obtain a quotation with lead time for production planning purposes.	
	13	
Country of Origin: None	Length (Min): 0.170	
Product Family: Capacitors	Length (Max): 0.200	
Product Subfamily: Capacitors Safety Caps	Width (Min):0.070	
Capacitance Value: 15.000	Width (Max): 0.090	
Cap Unit of Meas: pF	Part Weight (mg): 80.00	
Tolerance: ±5%	Packaged Width (lb) Arm: None	
Voltage: 3000.0	Packaging: 7" Reel Embossed Tape	
Dielectric Temp Coefficient: NP0/C0G	Packaging Qty: 2000	
Termination: 68	Operating Temp Range: -55°C to +125°C	
Marking: Required Safety Mark	Storage Temp Range (Packaged): -65°C to +125°C	
	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%	
Product Release Date: Jan. 9, 2006, 8 a.m.		
Web	Page	Link:
https://www.johansondielectrics.com/ac-safety-capacitors		