

Johanson Part Number Information

Johanson Part Number: 7350BP39A1950001E	Johanson Company: JTI
Legacy P/N: 7350BP39A1950E	Size for Capacitors (EIA): None
Description: Band Pass Filters, 1008, 6500-8500MHz, 0.5W, 3.0dB, Ni/Sn (RoHS), , 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 0	Thickness (Max): 0.039
Schedule B: 8534	Thickness (Min): 0.031
ITAR: 0	End Band(Min): 0.00
ECCN: EAR99	End Band (max): 0.020
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
REACH: 1	Lead Time Typical (Weeks)*:*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): 0.090
Product Family: Integrated Passive Components	Length (Max): 0.106
Product Subfamily: Band Pass Filters	Width (Min):0.071
Capacitance Value: None	Width (Max): 0.087
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 3000
Termination: 0	Operating Temp Range: -40°C to +105°C
Marking: Special	Storage Temp Range (Packaged): -65°C to +125°C
Product Release Date: June 2, 2020, 7 a.m.	Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%
Web	Page
Link:	
https://johansontechnology.com/band-pass-filters	