

Johanson Part Number Information

Johanson Part Number: 2450AT42E010B002E	Johanson Company: JTI
Legacy P/N: 2450AT42E010BE-AEC	Size for Capacitors (EIA): None
Description: Antennas, 2008, 2400-2480MHz, 2W max.W, -1.0 or -1.2dBi (typ), , Ni/Sn (RoHS), 7" Reel	Specification Number: None
Embossed Tape, AEC Q200 Qualified	
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 1	Thickness (Max): 0.067
Schedule B: 8529	Thickness (Min): 0.051
ITAR: 0	End Band(Min): None
ECCN: EAR99	End Band (max): None
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 1
	Lead Time Typical (Weeks)*:*This can vary significantly so it is
REACH: 0	important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): 0.189
Product Family: Antennas	Length (Max): 0.205
Product Subfamily: Antennas	Width (Min):0.071
Capacitance Value: None	Width (Max): 0.087
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 2000
Termination: 0	Operating Temp Range: -40°C to +125°C
Marking: Orientation Mark	Storage Temp Range (Packaged): -55°C to +125°C
Product Release Date: None	Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%
Web	Page
https://www.johansontechnology.com/antennas	Link: