

Johanson Part Number Information

Johanson Part Number: 3600BP15P0600001E

Legacy P/N: 3600BP15P0600E

Description: Band Pass Filters, 805, 3300-3900MHz,
3W, 1.8dB, Ni/Sn (RoHS), 3.6 GHz Band Pass Filter,
EIA 0805, SMD, Low Loss and High Attenuation, 7"

Reel Embossed Tape

Life Cycle Stage:

AEC Q200 Qualified: 0

Schedule B: 8534

ITAR: 0

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Band Pass Filters

Capacitance Value: None

Cap Unit of Meas: None

Tolerance: None

Voltage: None

Dielectric Temp Coefficient: None

Termination: 0

Marking: Special

Product Release Date: Nov. 12, 2019, 8 a.m.

Web Page Link: None

Johanson Company: JTI

Size for Capacitors (EIA): None

Specification Number: None

NCNR: 0

Thickness (Max): 0.041

Thickness (Min): 0.033

End Band(Min): 0.04

End Band (max): 0.055

Standard Item: 0

Lead Time Typical (Weeks)*:*This can vary significantly so it is

important to obtain a quotation with lead time for production planning purposes.

14

Length (Min): 0.073

Length (Max): 0.085

Width (Min):0.045

Width (Max): 0.053

Part Weight (mg): None

Packaged Width (lb) Arm: None

Packaging: 7" Reel Embossed Tape

Packaging Qty: 4000

Operating Temp Range: -40°C to +105°C

Storage Temp Range (Packaged): -40°C to +105°C

Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%