

Johanson Part Number Information

Johanson Part Number: 5550BP14A0800002T	Johanson Company: JTI
Legacy P/N: 5550BP14A0800T-AEC	Size for Capacitors (EIA): None
Description: Band Pass Filters, 0603, 5150-5950MHz, 1W, 0.9dB, 5GHz Low Profile Band Pass Filter, Ni/Sn (RoHS), 7" Reel Paper Tape, AEC Q200	Specification Number: None
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 1	Thickness (Max): 0.024
Schedule B: 8534	Thickness (Min): None
ITAR: 0	End Band(Min): 0.01
ECCN: EAR99	End Band (max): 0.014
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
	Lead Time Typical (Weeks)*:*This can vary significantly so it is
REACH: 1	important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): 0.057
Product Family: Integrated Passive Components	Length (Max): 0.069
Product Subfamily: Band Pass Filters	Width (Min):0.025
Capacitance Value: None	Width (Max): 0.037
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): -65°C to +125°C
Product Release Date: Oct. 21, 2015, 7 a.m.	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%
Web	Page
Link:	
https://johansontechnology.com/band-pass-filters	