

Johanson Part Number Information

Johanson Part Number: 3750BP07A0900001T

Legacy P/N: 3750BP07A0900T

Description: Band Pass Filters, 402, 3300-4200MHz, 3 max.W, 2.3dB, Ni/Sn (RoHS), 3.75GHz Band Pass Filter, EIA 0402, SMD, Low Loss and High Attenuatio, 7" Reel Paper Tape

Life Cycle Stage:

AEC Q200 Qualified: 0

Schedule B: 8534

ITAR: 0

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Band Pass Filters

Capacitance Value: None

Cap Unit of Meas: None

Tolerance: None

Voltage: None

Dielectric Temp Coefficient: None

Termination: 0

Marking: Special

Product Release Date: Dec. 14, 2020, 8 a.m.

Web Page Link: None

Johanson Company: JTI

Size for Capacitors (EIA): None

Specification Number: None

NCNR: 0

Thickness (Max): 0.012

Thickness (Min): None

End Band(Min): 0.01

End Band (max): 0.005

Standard Item: 0

Lead Time Typical (Weeks)*: *This can vary significantly so it is

important to obtain a quotation with lead time for production planning purposes.

14

Length (Min): 0.037

Length (Max): 0.041

Width (Min): 0.018

Width (Max): 0.022

Part Weight (mg): None

Packaged Width (lb) Arm: None

Packaging: 7" Reel Paper Tape

Packaging Qty: 10000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -40°C to +85°C

Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%