

MQDEC-409SR-PUR

DOUBLE-ENDED CORDSETS



Cordset: Double Ended M12
4-pin Straight Male; 4-pin Right-Angle Female
3 m 4x22 Black PUR Jacket
Nickel-Plated Brass Coupling Nuts
料件編號: 81292



PRODUCT SPECIFICATIONS:

Cable Jacket Color	Black
Connector 1 Key Code	A
Cable Jacket Material	PUR
Connector 2 Number of Contacts	4
Coupling Nut Material	Nickel Plated Brass
Connector 2 Key Code	A
Connector 1 Gender	Male
Connector 1 Orientation	Straight
Cordset Length (m)	3.00
Connector 2 Gender	Female
Outside Cable Diameter (mm)	4.06
Connector 1 Number of Contacts	4
Number of Ends	Double Ended
Connector 2 Type	M12
Connector 1 Type	M12
IP Rating	IP67
Connector 2 Orientation	Right Angle
Voltage Rating (V)	250 V ac/dc
Minimum Temp. (Celsius)	-40
Trunk Length (m)	No Trunk
Shield/No Shield	No Shield
Overmold Material and Color	PUR Black
Current Rating (A)	4.0
Maximum Temp. (Celsius)	70
Cordset Length Range (m)	2.00-4.99
Oil/Grease Resistant	Yes