

Johanson Part Number Information

Johanson Part Number: SCEF502W151K4GV001U	Johanson Company: JDI	
Legacy P/N: 502S47W151KV3U-****-SC	Size for Capacitors (EIA): 2220	
Description: Capacitors Safety Caps PME, 2220, X7R, 5,000.00V, 150.00pF±10% cap, Ni/Sn (RoHS) cap, 13" Reel Embossed Tape cap	Specification	Number:
Life Cycle Stage:	UL60950,EN/UL/IEC60384-14	
AEC Q200 Qualified: 0	NCNR: 0	
Schedule B: 8532	Thickness (Max): 0.150	
ITAR: 0	Thickness (Min): None	
ECCN: EAR99	End Band(Min): 0.01	
RoHS Compliance: Yes, RoHS 10/10	End Band (max): 0.040	
	Standard Item: 1	
	Lead Time Typical (Weeks)*:*This can vary significantly so it is	
REACH: 1	important to obtain a quotation with lead time for production planning purposes.	
	13	
Country of Origin: None	Length (Min): 0.210	
Product Family: Capacitors	Length (Max): 0.240	
Product Subfamily: Capacitors Safety Caps	Width (Min):0.185	
Capacitance Value: 150.000	Width (Max): 0.215	
Cap Unit of Meas: pF	Part Weight (mg): 520.00	
Tolerance: ±10%	Packaged Width (lb) Arm: None	
Voltage: 5000.0	Packaging: 13" Reel Embossed Tape	
Dielectric Temp Coefficient: X7R	Packaging Qty: None	
Termination: 68	Operating Temp Range: -55°C to +125°C	
Marking: Required Safety Mark	Storage Temp Range (Packaged): -65°C to +125°C	
Product Release Date: Jan. 3, 2006, 8 a.m.	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%	
Web	Page	Link:
https://www.johansondielectrics.com/ac-safety-capacitors		