

# Johanson Part Number Information

Johanson Part Number: 2600BP41A0400001E	Johanson Company: JTI
Legacy P/N: 2600BP41A0400E	Size for Capacitors (EIA): None
Description: Band Pass Filters, 1210, 2393-2793MHz, 3W, 2.6dB, , 2.6GHz Band Pass Filter, EIA 1210, SMD, High Attenuation, 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 0	Thickness (Max): 0.039
Schedule B: 8534	Thickness (Min): None
ITAR: 0	End Band(Min): None
ECCN: EAR99	End Band (max): None
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
REACH: 1	Lead Time Typical (Weeks)*:*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): 0.118
Product Family: Integrated Passive Components	Length (Max): 0.134
Product Subfamily: Band Pass Filters	Width (Min):0.090
Capacitance Value: None	Width (Max): 0.106
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 2000
Termination: None	Operating Temp Range: -40°C to +105°C
Marking: Special	Storage Temp Range (Packaged): None
Product Release Date: Sept. 25, 2007, 7 a.m.	Storage Temp Range (None Operating): +5°C to +35°C with RH 55% to 75%
Web	Page
Link:	
<a href="https://johansontechnology.com/band-pass-filters">https://johansontechnology.com/band-pass-filters</a>	