

Johanson Part Number Information

Johanson Part Number: 2450BP07C0100001T

Legacy P/N: 2450BP07C0100T

Description: Band Pass Filters, 402, 2400-2500MHz,
2W, 2.0dB, Ag/Pt (RoHS), Mini 2.4GHz Band Pass
Filter, EIA 0402, 7" Reel Paper Tape

Life Cycle Stage:

AEC Q200 Qualified: 0

Schedule B: 8534

ITAR: 0

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Band Pass Filters

Capacitance Value: None

Cap Unit of Meas: None

Tolerance: None

Voltage: None

Dielectric Temp Coefficient: None

Termination: 0

Marking: Special

Product Release Date: May 22, 2020, 7 a.m.

Web Page Link: None

Johanson Company: JTI

Size for Capacitors (EIA): None

Specification Number: None

NCNR: 0

Thickness (Max): 0.017

Thickness (Min): 0.013

End Band(Min): 0.00

End Band (max): 0.011

Standard Item: 0

Lead Time Typical (Weeks)*:*This can vary
significantly so it is

important to obtain a quotation with lead time
for production planning purposes.

14

Length (Min): 0.037

Length (Max): 0.041

Width (Min):0.018

Width (Max): 0.022

Part Weight (mg): None

Packaged Width (lb) Arm: None

Packaging: 7" Reel Paper Tape

Packaging Qty: 10000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -40°C to +85°C

Storage Temp Range (None Operating): +5°C to
+35°C with RH 45% to 75%