

Johanson Part Number Information

Johanson Part Number: 1850LP16A0105001E	Johanson Company: JTI
Legacy P/N: 1850LP16A0105E	Size for Capacitors (EIA): None
Description: Low Pass Filters, 0806, 1805-1910MHz, 4W, 0.4dB, 1.85GHz Low Pass Filter, extra attenuation behavior, Ni/Sn (RoHS), 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 0	Thickness (Max): 0.045
Schedule B: 8534	Thickness (Min): None
ITAR: 0	End Band(Min): None
ECCN: EAR99	End Band (max): None
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
	Lead Time Typical (Weeks)*:*This can vary significantly so it is
REACH: 1	important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): None
Product Family: Integrated Passive Components	Length (Max): None
Product Subfamily: Low Pass Filters	Width (Min):None
Capacitance Value: None	Width (Max): None
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): -65°C to +125°C
Product Release Date: None	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%
Web	Page
Link:	
https://johansontechnology.com/low-pass-filters	