

Johanson Part Number Information

Johanson Part Number: 2025LP15B0145001E	Johanson Company: JTI
Legacy P/N: 2025LP15B0145E	Size for Capacitors (EIA): None
Description: Low Pass Filters, 805, 800-1000/1700-1910/2010-2025MHz, 2 max.W, 0.5/0.8/1.5dB, Ni/Sn (RoHS), , 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 0	Thickness (Max): 0.039
Schedule B: 8534	Thickness (Min): None
ITAR: 0	End Band(Min): 0.03
ECCN: EAR99	End Band (max): 0.041
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
	Lead Time Typical (Weeks)*:*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.
REACH: 1	14
Country of Origin: TW	Length (Min): 0.073
Product Family: Integrated Passive Components	Length (Max): 0.085
Product Subfamily: Low Pass Filters	Width (Min):0.045
Capacitance Value: None	Width (Max): 0.053
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): -65°C to +125°C
Product Release Date: Feb. 9, 2018, 8 a.m.	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%
Web Page Link: None	