

# Johanson Part Number Information

Johanson Part Number: 2450BP14G0100001T	Johanson Company: JTI
Legacy P/N: 2450BP14G0100T	Size for Capacitors (EIA): None
Description: Band Pass Filters, 0603, 2400-2500MHz, 0.5W, 2dB, 2.45GHz High Rejection Band Pass Filter, Specification Number: None	
Ag/Pt (RoHS), 7" Reel Paper Tape	
Life Cycle Stage:	NCNR: 0
AEC Q200 Qualified: 0	Thickness (Max): 0.028
Schedule B: 8534	Thickness (Min): 0.020
ITAR: 0	End Band(Min): 0.02
ECCN: EAR99	End Band (max): 0.034
RoHS Compliance: Yes, RoHS 10/10	Standard Item: 0
	Lead Time Typical (Weeks)*:*This can vary significantly so it is
REACH: 1	important to obtain a quotation with lead time for production planning purposes.
	14
Country of Origin: TW	Length (Min): 0.059
Product Family: Integrated Passive Components	Length (Max): 0.067
Product Subfamily: Band Pass Filters	Width (Min):0.027
Capacitance Value: None	Width (Max): 0.035
Cap Unit of Meas: None	Part Weight (mg): None
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Paper Tape
Dielectric Temp Coefficient: None	Packaging Qty: 4000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Special	Storage Temp Range (Packaged): -65°C to +125°C
Product Release Date: None	Storage Temp Range (None Operating): +5°C to +40°C with RH 20% to 70%
Web	Page
	Link:
<a href="https://johansontechnology.com/band-pass-filters">https://johansontechnology.com/band-pass-filters</a>	