

# Johanson Part Number Information

Johanson Part Number: 2450LP05A0100001T

Legacy P/N: 2450LP05A0100T

Description: Low Pass Filters, 0202, 2400-2500MHz,  
3W, 0.45dB, Ni/Sn (RoHS), Low Pass Filter, 7" Reel

Paper Tape

Life Cycle Stage:

AEC Q200 Qualified: 0

Schedule B: 8534

ITAR: 0

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Low Pass Filters

Capacitance Value: None

Cap Unit of Meas: None

Tolerance: None

Voltage: None

Dielectric Temp Coefficient: None

Termination: 0

Marking: Special

Product Release Date: Sept. 20, 2021, 7 a.m.

Web

Page

Link:

<https://www.johansontechnology.com/low-pass-filters>

Johanson Company: JTI

Size for Capacitors (EIA): None

Specification Number: None

NCNR: 0

Thickness (Max): 0.016

Thickness (Min): None

End Band(Min): None

End Band (max): None

Standard Item: 1

Lead Time Typical (Weeks)\*:\*This can vary significantly so it is

important to obtain a quotation with lead time for production planning purposes.

14

Length (Min): 0.022

Length (Max): 0.030

Width (Min):0.016

Width (Max): 0.024

Part Weight (mg): None

Packaged Width (lb) Arm: None

Packaging: 7" Reel Paper Tape

Packaging Qty: 10000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -40°C to +85°C

Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%