



Glassfibre insulated ANSI Exposed Junction Thermocouple with Miniature Plug

- Type K, 300mm

XE-0457-001



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

General Description	Fast response welded exposed junction. Good temperature resistance (not suitable in fluids)
Thermocouple Type	K
Thermocouple Junction	Exposed
Cable Length	300mm
Cable Type	glassfibre insulated flat pair cable
Core / Strands	1/0.315mm
Cable Termination	Miniature Plug
Max. Temperature	+350°C (short periods up to 400°C)
Min. Temperature	-60°C
Standards Met	ANSI

Ordering Information

Thermocouple Type	Colour Code	Core/Strands	Length	Termination	Order Number
K	ANSI	1/0.315mm	300mm	Mini Plug	XE-0457-001