





P2

Pin Assignment

P1	P2
CC A5	A5
D+ A6	A6
D- A7	A7
SBU1 A8	A8
Vconn B5	B5
SBU2 B8	B8
TX1+ A2	A2
TX1- A3	A3
RX2+ A11	A11
RX2- A10	A10
TX2+ B2	B2
TX2- B3	B3
RX1+ B11	B11
RX1- B10	B10
GND (A1,A12,B1,B12)	A1,A12,B1,B12
Shell	Shell
VBUS (A4,A9,B4,B9)	A4,A9,B4,B9

ELECTRICAL TEST:

- 1.100% OPEN & SHORT & MIS WIRE TEST
 - 2.CONTACT RESISTANCE:2 OHM(MAX)
 - 3.INSULATION RESISTANCE:10M OHM(MIN)
 - 4.HI-POT TEST:DC 300V/10ms
- Supported Maximum Resolution 4K/30HZ



8	45P PVC Color:White	10	g	TOLERANCE INCHES M/M				CompuCableUSA TITLE: UTC-CUV05(TYPE CM To CF+VGA F +USB3.0 AF) CUSTOMER : CUSTOMER P/N : UC3-CMFA2 SCALE NONE UNIT MM DATE 2018.07.20 DRAWING NO.: REV. A01 1/1			
7	Transparent PE	2	g								
6	USB3.1 TYPE C Tinplate Shell Nickel Plated	1	pcs								
5	USB3.1 TYPE C ABS Shell Color:White	1	pcs								
4	USB3.1 C Type Connector With PCB Shell Nickel Plated	1	pcs	DRAWN BY CHECK BY APPD BY							
3	UTC-CUV05 ABS Shell Color:White	1	pcs								
2	UTC-CUV05(VL101) With PCB	1	pcs								
1	USB 3.1 [34AWG(7/0.06TC)+EAM]*4P+34AWG(7/0.06TC)*2C+28AWG(7/0.127TC)*2C+34AWG(7/0.06TC)*4C+AB(16/9/0.06 75%TC) OD: 3.9MM Color: White	0.16	m								
NO	DESCRIPTION	Q' TY	UNIT								