

**ModuPlug
HDC MRJ45 A MI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MRJ45 A MI
Order No.	2592220000
Version	Module, Plug insert, RJ45 tool-free, TIA-568A
GTIN (EAN)	4050118602333
Qty.	1 pc(s).

ModuPlug HDC MRJ45 A MI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.21 g
------------	--------

Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
------------	--

General data

Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Insulation strength	10 ¹² Ω
Material	Polycarbonate, glass fibre reinforced	Number of poles	8
Plugging cycles	750 (RJ45)	Pollution severity	3
Rated current (DIN EN 61984)	1 A	Rated impulse voltage (DIN EN 61984)	0.8 kV
Rated voltage (DIN EN 61984)	50 V	Required plug-in slots	1
Series	ModuPlug	Surge voltage category	III
Type	Pin	UL 94 flammability rating	V-0

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
eClass 9.0	27-44-02-92	eClass 9.1	27-44-02-18
eClass 10.0	27-44-02-92		

Downloads

Engineering Data	STEP
------------------	----------------------

ModuPlug HDC MRJ45 A MI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

