



Pan-Ty® PRWP1.5S-D0 Releasable Wing Push Mount Tie, Black, UV PA6.6, 6.8"L, 50lb

PRWP1.5S-D0

Panduit PRWP1.5S-D0 Releasable Wing Push Mount Ties use an all-in-one design to attach bundles to another surface using a stable, secure, rattle-free installation. Extended release tab permits easy release and re-use where changes are anticipated during development, production or servicing in the field. Standard cross section, 6.8" (173mm) length. For indoor or outdoor use, made of Weather Resistant Nylon 6.6, with high resistance to ultraviolet light are black in color and come in packages of 500

Specifications

Product Type	Premium Cable Tie
Color	Black
Environment	Indoor/Outdoor
Material	Nylon 6.6
Resistance Properties	UV-Resistant, Weather-Resistant
Overall Length (In.)	6.8
Overall Length (mm)	173
Body Width (In.)	0.19
Body Width (mm)	4.8
Maximum Bundle Diameter (In.)	1.5
Maximum Bundle Diameter (mm)	38.1
Minimum Bundle Diameter (In.)	0.06
Minimum Bundle Diameter (mm)	1.5
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL 62275 Compliant (Type 1, 11), UL Recognized (File #E56854), RoHS, CE Complaint
For Use With	Hand Install Only

Packaging Detail

UPC	07498357007
Std. Pkg. Qty.	500
Std. Pkg. Volume (cf)	0.2559
Std. Ctn. Qty.	5000
Std. Ctn. Volume (cf)	2.5587