








# SERPAC RB55X14Y10Y 2

Electronic Enclosures



**RB55X14C16C 2**  
(Part shown, no material (X) specified)


PN	Description
RB55-X14Y	(1) RB55X14Y, Top
RB55X10Y	(1) RB55X10Y, Bottom
8055	(1) RB55 O-Ring
6052	(4) #6-32 CaptivePH Hd Screw
6022	(4) #10 High/Low Pan Hd x 1/4"
6113	(4) #6-32 Threaded Insert

1 =INTERIOR DIMENSIONS (@ BOTTOM)  
2 =STANDARD COLORS (Y) ARE: BLACK (B), CLEAR (C) AND GRAY (G)  
 TOPS AND BOTTOMS ALL POSSIBLE COMBINATIONS AVAILABLE  
 STANDARD MATERIALS (X) IS: POLYCARBONATE (P)  
 -Watertight enclosure meets or exceed Nema 4 and or IP67.

Dimensions represent Polycarbonate material.  
 Dim's in Inch [ mm]

ALL DIMENSIONS ARE ± .010" 5/5/2023  
 2009 Wright Street, La Verne, Ca. 91750  
 Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

# RB55 Circuit Board (Fits all Parts starting with RB55)



(REFERENCE ONLY)