

DEE2R-575D

DOUBLE-ENDED CORDSETS



Cordset: Double Ended M12
5-pin Straight Female; 5-pin Straight Male
22.9 m 5x22 Yellow PVC Jacket
Nickel-Plated Brass Coupling Nuts
Part Number: 72338

SPECIFICATIONS

Connector 2 Gender	Male
Cordset Length (m)	22.90
Outside Cable Diameter (mm)	5.50
Connector 1 Gender	Female
Connector 2 Key Code	A
Connector 1 Orientation	Straight
Shield/No Shield	No Shield
Cordset Length Range (m)	Greater than 20.00
Cable Jacket Material	PVC
Connector 2 Orientation	Straight
Connector 2 Type	M12
Connector 1 Type	M12
Number of Ends	Double Ended
Connector 1 Number of Contacts	5
Connector 2 Number of Contacts	5
Coupling Nut Material	Nickel Plated Brass
IP Rating	IP67
Cable Jacket Color	Yellow
Connector 1 Key Code	A
Overmold Material and Color	PUR Black
Current Rating (A)	4.0
Voltage Rating (V)	250 V ac/dc
Minimum Temp. (Celsius)	-40
Trunk Length (m)	No Trunk

Maximum Temp. (Celsius)	70
-------------------------	----