DEE2R-8100D

DOUBLE-ENDED CORDSETS

Cordset: Double Ended M12

8-pin Straight Female; 8-pin Straight Male

30.48 m 8x22 Yellow PVC Jacket

Nickel-Plated Brass Coupling Nuts

Part Number: 72211

CERTIFICATIONS

SPECIFICATIONS

Connector 2 Gender	Male
Cordset Length (m)	30.48
Outside Cable Diameter (mm)	5.46
Connector 1 Gender	Female
Connector 2 Key Code	A
Connector 1 Orientation	Straight
Shield/No Shield	No Shield
Cordset Length Range (m)	Greater than 20.00
Cable Jacket Material	PVC
Connector 2 Orientation	Straight
Connector 2 Type	M12
Connector 1 Type	M12
Number of Ends	Double Ended
Connector 1 Number of Contacts	8
Connector 2 Number of Contacts	8
Coupling Nut Material	Nickel Plated Brass
IP Rating	IP68
Cable Jacket Color	Yellow
Connector 1 Key Code	A
Overmold Material and Color	PUR Black
Current Rating (A)	2.0
Voltage Rating (V)	30 V ac/dc
Minimum Temp. (Celsius)	-40
Trunk Length (m)	No Trunk

Maximum Temp. (Celsius)	70