

DEE2R-83D

DOUBLE-ENDED CORDSETS



Cordset: Double Ended M12  
8-pin Straight Female; 8-pin Straight Male  
0.91 m 8x22 Yellow PVC Jacket  
Nickel-Plated Brass Coupling Nuts  
Part Number: 72206

CERTIFICATIONS



SPECIFICATIONS

|                                |                     |
|--------------------------------|---------------------|
| Connector 2 Gender             | Male                |
| Cordset Length (m)             | 0.91                |
| Outside Cable Diameter (mm)    | 5.46                |
| Connector 1 Gender             | Female              |
| Connector 2 Key Code           | A                   |
| Connector 1 Orientation        | Straight            |
| Shield/No Shield               | No Shield           |
| Cordset Length Range (m)       | Less than 2.00      |
| Cable Jacket Material          | PVC                 |
| Connector 2 Orientation        | Straight            |
| Connector 2 Type               | M12                 |
| Connector 1 Type               | M12                 |
| Number of Ends                 | Double Ended        |
| Connector 1 Number of Contacts | 8                   |
| Connector 2 Number of Contacts | 8                   |
| Coupling Nut Material          | Nickel Plated Brass |
| IP Rating                      | IP68                |
| Cable Jacket Color             | Yellow              |
| Connector 1 Key Code           | A                   |
| Overmold Material and Color    | PUR Black           |
| Current Rating (A)             | 2.0                 |
| Voltage Rating (V)             | 30 V ac/dc          |
| Minimum Temp. (Celsius)        | -40                 |
| Trunk Length (m)               | No Trunk            |
|                                |                     |

|                         |    |
|-------------------------|----|
| Maximum Temp. (Celsius) | 70 |
|-------------------------|----|