







| SIGN                                           | DATE       | DESCRIPTION                                             | APPROVER |
|------------------------------------------------|------------|---------------------------------------------------------|----------|
| △                                              | 2010.04.26 | The normal grey No. changed from RAL7004/P to RAL7035/D | Jacke    |
| △                                              | 2010.04.26 | The dimensions is changed from ① 1.40 to ① 1.60         | Jacke    |
| △                                              | 2010.06.19 | The design is changed                                   | Chen Bo  |
| △                                              | 2010.09.20 | The Material is changed from Brass to Copper            | Chen Bo  |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                                                         |          |

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ① Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 20A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: CEus

EU 04 70 x 0 xxxx G

- COLOR
- 0 Black (RAL9005)
  - 2 Red (RAL3001/D)
  - △ 3 Orange(RAL2011/P)
  - 4 Yellow(RAL1018/A)
  - 5 Green(RAL6018/T)
  - 6 Blue (RAL5015/A)
  - 8 Grey(RAL7035/D)

G: Pb<40,000ppm

0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |               |                            |                       |              |            |
|----------|---------------|----------------------------|-----------------------|--------------|------------|
| TITLE    |               | EU 5.0 SERIES 4P ( Right ) |                       |              |            |
| PART NO. | EU0470x0xxxxG |                            |                       | DWG NO.      | 8EU0003    |
| APPROVED | CHECKED       | DESIGNED                   | DRAWN                 | CUST NO.     |            |
|          |               |                            | Chen Bo<br>2010.09.20 |              | Tolerance  |
|          |               |                            |                       |              | X. ±0.50   |
|          |               |                            |                       |              | X.X ±0.30  |
|          |               |                            |                       |              | X.XX ±0.10 |
|          |               |                            |                       |              | X° ±1°     |
|          |               |                            |                       | SHEET: 01/01 | REV.: E    |