







| SIGN                                           | DATE       | DESCRIPTION                                               | APPROVER |
|------------------------------------------------|------------|-----------------------------------------------------------|----------|
| △                                              | 2010.04.26 | The normal grey No. changed from RAL7004/P to RAL7035/D   | Jacke    |
| △                                              | 2010.04.26 | The dimensions is changed from $\phi 1.40$ to $\phi 1.60$ | Jacke    |
| △                                              | 2010.06.19 | The design is changed                                     | Chen Bo  |
| △                                              | 2010.09.20 | The Material is changed from Brass to Copper              | Chen Bo  |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                                                           |          |

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ⑥ Terminal(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 20A
- Withstanding Voltage: 1.6 KV
- Operating temperature:  $-40^{\circ}\text{C}$  to  $+115^{\circ}\text{C}$
- Soldering temperature:  $250^{\circ}\text{C} \pm 10^{\circ}\text{C}/5 \text{ Sec}$
- Safety Approval: us

EU 03 70 x 0 xxxx G

COLOR


- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- △ 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)

G: Pb<40,000ppm  
0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by customer request, please contact sales department.

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                            |          |                       |                                                                                       |             |         |       |           |    |
|----------|----------------------------|----------|-----------------------|---------------------------------------------------------------------------------------|-------------|---------|-------|-----------|----|
| TITLE    | EU 5.0 SERIES 3P ( Right ) |          |                       |                                                                                       |             |         |       |           |    |
| PART NO. | EU0370x0xxxxG              |          |                       |                                                                                       | DWG NO.     | 8EU0001 |       |           |    |
| APPROVED | CHECKED                    | DESIGNED | DRAWN                 | CUST NO.                                                                              |             |         |       | Tolerance |    |
|          |                            |          | Chen Bo<br>2010.09.20 |  |             |         |       | UNIT: mm  | X. |
|          |                            |          |                       |                                                                                       | SCALE: NONE | X.X     | ±0.30 |           |    |
|          |                            |          |                       | SHEET: 01/01                                                                          | REV.: E     | X.XX    | ±0.10 |           |    |
|          |                            |          |                       |                                                                                       |             | X°      | ±1°   |           |    |