





PANEL CUT-OUT

标准治具實配



THICKNESS	C
0.8t-1.0t	19.8
1.0t-1.2t	19.9
1.2t-1.5t	19.9
2t	20.0
3.5t	20.1


SPECIFICATION:

1. INSULATION RESISTANCE: OVER $100M\Omega$ 500V DC.
2. DIELECTRIC STRENGTH: 2000V AC ONE MINUTE.
3. Body Material: Black Glass-Fiber Thermoplastic . UL 94V-2~0

Rating:AC 15A 250V	
Mark	Safety Regulation
UL	UL
cUL	CUL
Rating:AC 10A 250V	
Mark	Safety Regulation
VDE	VDE
CCC	CCC
ENEC	ENEC



富灣(佛岡)五金電器有限公司
RICH BAY INT'L LTD.
廣東省清遠市佛岡縣城南工業區
South Town Industrial Area of Fogong County
Qing Yuan City Guangdong Province, China
TEL:0763-4289946 FAX:0763-4288096



UNIT

mm

UNIT Q'TY

1

SCALE

1:1

TOLERANCE

$X.XX \pm 0.1$
 $XX.XX \pm 0.2$
 $XXX.XX \pm 0.3$

PRODUCT NO.

R-301SN(B00)-Z

REV

DRAWN BY

李

APPROVED BY

宋

ID NO

19052004Q

INTERIM NO.

NEW NO.

DESCRIPTION

A