





XX	A
12	1.2
15	1.5
17	1.7
20	2.0
25	2.5




B		
R-306SN(00)XX	R-306SN(01)XX	R-306SN(02)XX
C		
(36.0)	(36.0)	(35.5)

- SPECIFICATION:**
1. Insulation Resistance: Over 100MΩ at 500V DC
 2. Dielectric strength: 2000V AC 1 Minute.
 3. Body Material: Thermoplastic 94V-2~V-0.


Rating:AC 16A 250V	
Mark	Safety Regulation
	VDE
Rating:AC 20A 250V	
Mark	Safety Regulation
	CULUS



富灣股份有限公司
RICH BAY COMPANY LTD.
台北縣樹林市東興街57號
NO. 57, Tung Hsing St., Shu-Lin Town,
Taipei Hsien, Taiwan, R. O. C.
TEL:886-2-86867781~4 FAX:886-2-86867780
http://www.richbay.com.tw



DRAWN BY



UNIT

mm

UNIT Q'TY

1

SCALE

1:1

APPROVED BY



TOLERANCE

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

DESCRIPTION

220705A01

PRODUCT NO.

INTERIM NO.

NEW NO.

R-306SN(00) XX

REV

F