









PRODUCT NO.	COLOR
RU-02-B04-14R	RED
RU-02-B04-14L	BLUE
RU-02-B04-14W	WHITE
RU-02-B04-14	BLACK



P/N	PART NAME	NO REQ	MATERIAL & SPEC
1	"GRN" TERMINAL	1	Brass 0.4t
2	"WHT" TERMINAL	1	Brass 0.4t, NI plating
3	"BLK" TERMINAL	1	Brass 0.4t

SPECIFICATION:

1. Insulation Resistance: Over 100MΩ at 500V DC.
2. Dielectric strength: 2000V AC 1 Minute.
3. Body Material: Thermoplastic 94V-2~V-0.
4. Use Wire Size :14AWG Solid Conductor

Rating: AC 15A 125V	
Mark	Safety Regulation
	CULUS



富灣股份有限公司
RICH BAY COMPANY LTD.
台北縣樹林市東興街57號
NO. 57, Tung Hsing St., Shu-Lin Town,
Taipei Hsien, Taiwan, R. O. C.
TEL: 886-2-86867781~4 FAX: 886-2-86867780
http://www.richbay.com.tw

	UNIT	UNIT QTY	SCALE	TOLERANCE X.XX±0.1 XX.XX±0.2 XXX.XX±0.3		PRODUCT NO.	RU-02-B04-14	REV
	mm	1	3:2					
DRAWN BY		APPROVED BY		ID NO	200109A06	INTERIM NO.		A
				DESCRIPTION		NEW NO.		

