



.233
[5.92]




RECOMMENDED
MOUNTING HOLE

RevNo	Revision Notes	Date	Checked
1	RoHS Compliant	051105	PC
2	Frequency Range added	061013	GC

5/16 HEX NUT



1/4-36UNS-2A
(x2)



RoHS Compliant

MATERIALS

BODY	BRASS
BODY PLATING	GOLD
CONTACT	PHOSPHOR BRONZE
CONTACT PLATING	GOLD
DIELECTRIC	TEFLON (PTFE)

50 Ohm IMPEDANCE
500V PEAK VOLTAGE RATING
TEMPERATURE RANGE: -55°C TO +155°C
FREQUENCY RANGE: 0 to 18 GHz
INTERFACE DIMENSIONS SIMILAR TO MIL-C-39012

MILLIMETER WAVE TECHNOLOGIES
6501 W. FRYE ROAD, #23
CHANDLER, AZ 85226

ADAPTOR
SMA JACK to SMA BULKHEAD JACK

Designed by N. JAIN	Checked by W. CANON	Approved by A. LEE	File name MW-632-BH	TITLE MW-632-BH
TOLERANCES DIMENSIONS IN INCHES UNLESS OTHERWISE SPECIFIED DECIMALS .XX ± .02 .XXX ± .005 ANGULAR ± .06				REV. 2 DATE 060601
ALL DIMENSIONS ON THIS DRAWING ARE FOR REFERENCE PURPOSES ONLY AND ARE SUBJECT TO CHANGE.				Scale NONE Sheet 1 of 1