

Stainless Steel Tooth Metal-Lock Nylon Cable Ties

Hayata features a full line of high tensile strength metal-lock nylon ties with a robust stainless steel tooth for more precise and long lasting tie-lock.



- Smooth rounded-style head
- Stainless Steel locking tooth provides infinite adjustability through its entire bundle range
- Low thread force reduces installer fatigue
- High tensile strength exceeds industry standards
- Wide variety of sizes including 18 lbs. to 120 lbs. in Natural, Black and other colors to meet your bundling needs
- Available in lengths from 4" (100mm) – 27.5" (700mm)



NATURAL	BLACK UV	LENGTH		WIDTH		MAXIMUM BUNDLE DIAMETER		MINIMUM LOOP TENSILE	RECOMMENDED HAYATA TOOL	PACKAGING			
Part No.*	Part No.*									STD. BAG QTY.	STD. CASE QTY.*	BULK BAG QTY.*	BULK CTN. QTY.
STNC100-18	STNC100-18B	4	100	.110	3.0	0.87	22	18	TG-3, TG-7	100	1,000	1,000	25,000
STNC200-18	STNC200-18B	8	201	.100	2.4	2.00	51	18	TG-3, TG-7	100	1,000	1,000	25,000
STNC150-40	STNC150-40B	6	155	.141	3.6	1.38	35	40	TG-3, TG-7	100	1,000	1,000	20,000
STNC200-40	STNC200-40B	8	200	.157	4.0	2.09	53	40	TG-3, TG-7	100	1,000	1,000	10,000
STNC280-40	STNC280-40B	11	284	.142	3.6	3.15	80	40	TG-3, TG-7	100	1,000	1,000	10,000
STNC368-40	STNC368-40B	14.5	368	.142	3.6	4.09	104	40	TG-3, TG-7	100	1,000	1,000	10,000
STNC190-50	STNC190-50B	7.5	190	.188	4.8	1.77	45	50	TG-3, TG-7	100	1,000	1,000	10,000
STNC300-50	STNC300-50B	12	300	.196	5.0	3.00	76	50	TG-3, TG-7	100	1,000	1,000	5,000
STNC380-50	STNC380-50B	15	376	.196	5.0	3.94	100	50	TG-3, TG-7	100	1,000	1,000	5,000
STNC300-120	STNC300-120B	12	300	.275	7.0	3.00	76	120	TG-9	100	1,000	-	-
STNC380-120	STNC380-120B	15	380	.275	7.0	4.00	102	120	TG-9	100	1,000	-	-
STNC460-120	STNC460-120B	18	460	.275	7.0	5.00	127	120	TG-9	100	1,000	-	-
STNC540-120	STNC540-120B	21	540	.275	7.0	6.00	152	120	TG-9	100	1,000	-	-
STNC700-120	STNC700-120B	27.5	700	.275	7.0	8.00	203	120	TG-9	100	1,000	-	-

*To order Bulk (1,000/Bag):

- NATURAL: add "M" at end of part number (example: STNC100-18M)

- BLACK UV: add "M" before B example: STNC100-18MB



Smooth Head Design

- Rounded edges for easy handling
- Low-threading force required
- Faster installation and lower hand fatigue

Curved Tie Tip

- For faster threading
- Easy to pick up

High Tensile Strength

- Exceeds industry standards
- Available from 18 lbs. up to 120 lbs.

SS Tooth Cable Tie Tension Tools

Part #	Material	Tension Range	Color
TG-3	Metal	18 - 50 Lb	Blue
TG-7	Plastic	120 - 175 Lb	Blue
TG-9	Metal	120 - 175 Lb	Red

