


P1: M-084A
P2: M-007

Customer No.: No.1



1 FT LENGTH LABEL :

3 FT LENGTH LABEL :

≥ 6 FT LENGTH LABEL :



THE LABELED LENGTH
CHANGES
ACCORDING TO THE
ACTUAL LENGTH



MARKING:

(UL) SJT 3/C 16AWG(1.31MM²) VW-1 75°C 300V E204978 C(UL)
SJT 3/C 1.31MM²(16AWG) FT2 60°C 300V E204978 MSL-VN-

108158B2F16A(FP364-00)

P1 P2

L ——— L BLACK
N ——— N WHITE
E ——— E GREEN

P1,P2: cULus E210037-VN

*NOTE: ALL relevant materials are complied with RoHS directive.
THE MARKING IS CONCAVE LETTERING MOULD
LABEL B IS "WARNING LABEL"
LABEL A IS "UL LABEL"

3	UL SJT 16AWG*3C OD 8.5mm, JACKET BLACK, DRAWING No.EPSYT011603C-058	H5TC43-0304K09	L-30mm	M304
2	MOLDED PVC 45P, COLOR BLACK	H1BF01-0304K09		M304
	BRACKET: XWT-6180	A1QC15-1299W09	1	M1299
	TERMINAL: 98575BS-0	A1QB09-0257	1	M257
1	TERMINAL: 98752BS-0	A1QB11-0257	2	M257
	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
1	TERMINAL WITH BRACKET: LP-31M内紫-9	A1QC82-1035K09	1	M1035
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		CompuCableUSA Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED	HU			
DESIGNER	XJW			
DRAWING	MuMu			
DATE	12/JUL/24	ITEM NO.	AC-042XX	UNIT: mm

REV.3 2024.07.12 MODIFY P1 PLUG MODEL AND BRACKET SUPPLIER

REV.1 2021.11.09 MODIFY PLUG DESCRIPTION REV.2 2022.07.13 CANCEL P1 INTERNAL MODEL

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm