


P1: M-004

P2: M-005


Customer No.:



IEC 320 C14(MSL-106)

IEC 320 C13(MSL-107)

PACKING :



P/N	JACKET & MOLDED & BRACKET COLOR
AC -14-022XX	BLACK
AC -14-022XXRD	RED(PT201C)
AC -14-022XXBU	BLUE(PT286C)

MARKING:

(UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978 C(UL)
 SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978 MSL-VN-

	P1	P2
BLACK	L	L
WHITE	N	N
GREEN	E	E

P1,P2: E210037-VN

* NOTE: All relevant materials are complied with RoHS directive .
 THE MARKING IS PROTRUDING LETTERING MOULD

3	UL SJT 14AWG*3C, OD 9.3mm, JACKET BLACK, DRAWING No. EPSVT011403C-147	H5TC21-0304K09	L-40mm	M304
2	MOLDED PVC 35P, COLOR BLACK	HIBC02-0304K09		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm 98744L	A1QB42-0257	3	M257
1	MOLDED PVC 35P, COLOR BLACK	HIBC02-0304K09		M304
	BRACKET: YS-014	A1QC10-0767K09	1	M767
	TERMINAL: 2x4mm 98672BS-1	A1QB07-0257	3	M257
No.	DESCRIPTION		Q'TY	Supplier
APPROVED				
CHECKED	HU			
DESIGNER	XJW			
DRAWING	DAI			
DATE	13/SEP/23	ITEM NO.	AC-14-022XXXX	UNIT:mm

CompuCableUSA

Cable Length Unless Other Spec.
 Tolerances:
 0 ~200mm ±10mm
 201~1000mm ±20mm
 1001 ~1500mm ±25mm
 1501~2100mm ±30mm
 2100mm± ±40mm

REV.9 2023.09.13	MODIFY MARKING	REV.8 2022.03.18	MODIFY DIE SIZE AND PACKING
REV.7 2021.11.15	MODIFY MARKING	REV.6 2017.09.21	ADD P/N MOLDED COLOR
REV.5 2017.07.20	MODIFY CABLE & MOLDED GOLD	REV.4 2017.06.16	MODIFY MSL-107 TERMINA & MOLDED SIZE
REV.3 2017.05.11	MODIFY MODEL SIZE	REV.2 2015.03.04	MODIFY PLUG LOGO

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm