


P1: M-004

P2: M-005


Customer No.:



IEC 320 C14(MSL-106)

IEC 320 C13(MSL-107)

PACKING :



MARKING:

(UL) SJT 3/C 14AWG(2.08MM<sup>2</sup>) VW-1 105°C 300V E204978 C(UL)  
SJT 3/C 2.08MM<sup>2</sup>(14AWG) FT2 105°C 300V E204978 MSL-VN-

| P1    |   | P2 |   |
|-------|---|----|---|
| BLACK | L | L  | L |
| WHITE | N | N  | N |
| GREEN | E | E  | E |

| P/N           | JACKET & MOLDED & BRACKET COLOR |
|---------------|---------------------------------|
| AC-14-022XX   | BLACK                           |
| AC-14-022XXRD | RED(PT201C)                     |
| AC-14-022XXBU | BLUE(PT286C)                    |
| AC-14-022XXGN | GREEN(PT376C)                   |
| AC-14-022XXYE | YELLOW(PT123C)                  |
| AC-14-022XXWH | WHITE(W49)                      |

P1,P2: E210037-VN

\* NOTE: All relevant materials are complied with RoHS directive .  
THE MARKING IS PROTRUDING LETTERING MOULD

|     |                                                                       |                |        |          |
|-----|-----------------------------------------------------------------------|----------------|--------|----------|
| 3   | UL SJT 14AWG*3C, OD 9.3mm, JACKET BLACK, DRAWING No. EPSVT011403C-147 | H5TC21-0304K09 | L-40mm | M304     |
| 2   | MOLDED PVC 35P, COLOR BLACK                                           | H1BC02-0304K09 |        | M304     |
|     | BRACKET: YS-003                                                       | A1QC14-0767    | 1      | M767     |
| 1   | TERMINAL: 2*4mm 98744L                                                | A1QB42-0257    | 3      | M257     |
|     | MOLDED PVC 35P, COLOR BLACK                                           | H1BC02-0304K09 |        | M304     |
|     | BRACKET: YS-014                                                       | A1QC10-0767K09 | 1      | M767     |
|     | TERMINAL: 2x4mm 98672BS-1                                             | A1QB07-0257    | 3      | M257     |
| No. | DESCRIPTION                                                           | Q'TY           |        | Supplier |

|                  |                            |                   |                                                           |
|------------------|----------------------------|-------------------|-----------------------------------------------------------|
| REV.9 2023.09.13 | MODIFY MARKING             | REV.10 2025.04.07 | ADD CURRENT SYMBOL AND JACKET COLOR, MODIFY PUBLIC ERRAND |
| REV.7 2021.11.15 | MODIFY MARKING             | REV.8 2022.03.18  | MODIFY DIE SIZE AND PACKING                               |
| REV.5 2017.07.20 | MODIFY CABLE & MOLDED GOLO | REV.6 2017.09.21  | ADD P/N MOLDED COLOR                                      |
| REV.3 2017.05.11 | MODIFY MODEL SIZE          | REV.4 2017.06.16  | MODIFY MSL-107 TERMINA & MOLDED SIZE                      |
| REV.1 2011.11.14 | MODIFY CABLE MARKING       | REV.2 2015.03.04  | MODIFY PLUG LOGO                                          |

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

|          |           |                                                                                                                      |                             |  |                                                                              |         |                                                                                       |                                                                                       |
|----------|-----------|----------------------------------------------------------------------------------------------------------------------|-----------------------------|--|------------------------------------------------------------------------------|---------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| APPROVED |           | <div><b>CompuCable</b>USA</div> |                             |  | Cable Length Unless Other Spec.                                              |         |                                                                                       |                                                                                       |
| CHECKED  | HU        |                                                                                                                      |                             |  | Tolerances:                                                                  |         |                                                                                       |                                                                                       |
| DESIGNER | XJW       |                                                                                                                      |                             |  | 0 ~200mm ±10mm                                                               |         |                                                                                       |                                                                                       |
| DRAWING  | PLS       |                                                                                                                      |                             |  | 201~1000mm ±20mm<br>1001 ~1500mm ±25mm<br>1501~2100mm ±30mm<br>2100mm↑ ±40mm |         |                                                                                       |                                                                                       |
| DATE     | 07/APR/25 | ITEM NO.                                                                                                             | AC-14-022XX & AC-14-022XXXX |  |                                                                              | UNIT:mm |  |  |