


P1: M-084A

P2: M-007

Customer No.: No. 1



PACKING A: ≤1FT


PACKING B: ≤2FT

PACKING C: >2FT

1 FT LENGTH LABEL :

3 FT LENGTH LABEL :

≥ 6 FT LENGTH LABEL :

THE LABELED LENGTH
CHANGES ACCORDING TO
THE ACTUAL LENGTH

MARKING: (UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978
 C(UL) SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978 MSL-VN-

108158B2F14A(FP397-00)

P1 P2
 L L BLACK
 N N WHITE
 E E GREEN

P1,P2: E210037-VN

NOTE: All relevant materials are complied with RoHS directive .
 THE CABLE MARKING IS CONCAVE LETTERING MOULD
 LABEL B IS "WARNING LABEL"
 LABEL A IS "UL LABEL"

3	UL SJT 14AWG*3C OD 9.3mm, JACKET BLACK, DRAWING No. EPSVT011403C-147		H5TC21-0304K09	L-30mm	M304	
2	MOLDED PVC 45P, COLOR BLACK		H1BF01-0304K09		M304	
	BRACKET: XWT-6180		A1QC15-1299W09	1	M1299	
	TERMINAL: 98575BS-0		A1QB09-0257	1	M257	
	TERMINAL: 98752LBS-0		A1QB10-0257	2	M257	
1	MOLDED PVC 35P, COLOR BLACK		H1BC02-0304K09		M304	
	TERMINAL WITH BRACKET: LP-31M内装-9		A1QC82-1035K09	1	M1035	
No.		DESCRIPTION			Q'TY	Supplier
APPROVED		CompuCableUSA			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm± ±40mm	
CHECKED	HU					
DESIGNER	XJW					
DRAWING	MuMu					
DATE	12/JUL/24	ITEM NO.	AC-14-042XX			 UNIT: mm

CompuCableUSA

Cable Length
Unless Other Spec.
Tolerances:
 0 ~200mm ±10mm
 201~1000mm ±20mm
 1001 ~1500mm ±25mm
 1501~2100mm ±30mm
 2100mm ±40mm

REV.3 2024.07.12 MODIFY P1 PLUG MODEL AND P2 BRACKET SUPPLIER

REV.1 2022.07.13 CANCEL P1 INTERNAL MODEL REV.2 2023.08.30 MODIFY PLUG NAME AND MODIFY PLUG SUPPLIER

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm