




P1: M-004
P2,P3: M-005
P4: M-008

Customer No.: NO.1



PLUG: IEC 320 C14

PLUG: IEC 320 C13

PLUG: IEC 320 C13





PLUG: IEC 320 C13

③ P1,P2,P3: ④ E210037-VN
① P4: ② E210037-VN

② PACKING A: <0.8M

PACKING B: 0.8M~3M

PACKING C: >3M



MARKING:

⑤ ④ (UL) SJT 3/C 16AWG(1.31MM²) VW-1 105°C 300V E204978 C(UL)
SJT 3/C 1.31MM²(16AWG) FT2 105°C 300V E204978 MSL-VN-

	P1	P2	P3
BLACK	L	L	L
WHITE	N	N	N
GREEN	E	E	E

*NOTE: All relevant materials are complied with RoHS directive.
THE MARKING IS CONCAVE LETTERING MOULD

4	UL SJT 16AWG*3C OD 8.5mm, JACKET BLACK, DRAWING No. EPSVT011603C-059	H5TC04-0304K09	Lmm*1PCS Xmm*2PCS	M304
3	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-021	A1QC18-0767	1	M767
	TERMINAL: 96146BS-0	A1QB17-0257	3	M257
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-003	A1QC14-0767	2	M767
	TERMINAL: 2*4mm 98740BS-0/A	A1QB55-0257	6	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304K09		M304
	BRACKET: YS-014	A1QC10-0767	1	M767
	TERMINAL: 2x4mm 98672BS-1	A1QB07-0257	3	M257
No.	DESCRIPTION		Q'TY	Supplier

APPROVED

CHECKED

DESIGNER

DRAWING

HU

ZHU

QIN

CompuCableUSA

Cable Length Unless Other Spec.
Tolerances:
0 ~200mm ±10mm
201~1000mm ±20mm
1001 ~1500mm ±25mm
1501~2100mm ±30mm
2100mm↑ ±40mm

DATE 26/AUG/24

ITEM NO.

AC-141613Y-XX

UNIT:mm



REV.5 2023.10.23	MODIFY MARKING	REV.6 2024.8.26	MODIFY MOLDED LOGO AND SIZE
REV.3 2017.08.18	MODIFY CABLE MOLDED & MOLDED GOLO	REV.4 2023.02.23	MODIFY MARKING
REV.1 2016.04.11	MODIFY P4 LOGO	REV.2 2016.08.01	MODIFY PACKING
NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm			