


PACKING A: ≥1FT



PACKING B: ≥2FT



PACKING C: <2FT



PAGE : 2 OF 2

REV.2 2022.5.26 ADD MOLDED

REV.1 2021.12.25 MODIFY MARKING:

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm



LABEL A

1 FT LENGTH LABEL :



LABEL B BACK

LABEL B FRONT

3 FT LENGTH LABEL :



LABEL B BACK

LABEL B FRONT

≥ 6 FT LENGTH LABEL :



LABEL B BACK

LABEL B FRONT

THE LABELED LENGTH
CHANGES ACCORDING TO
THE ACTUAL LENGTH

*NOTE: ALL relevant materials are complied with RoHS directive.

No.	DESCRIPTION		Q'TY	Supplier
APPROVED				
CHECKED	HU			
DESIGNER	ZHU			
DRAWING	ZY			
DATE	26/MAY/22	ITEM NO.	AC-LP0420X	
		Cable Length Unless Other Spec. Tolerances:		
		0 ~200mm		±10mm
		201~1000mm		±20mm
		1001 ~1500mm		±25mm
		1501~2100mm		±30mm
		2100mm ↑		±40mm
		UNIT:mm		

CompuCableUSA